





FLUID AND FILTER CHANGE RECOMMENDATIONS

Use of the proper fluid and filters is the simplest thing that an owner can do to ensure the ongoing performance and reliability of Allison automatic transmissions. Allison Transmission has designed extensive specification and testing programs to verify the quality of fluids. As a result, the specific fluid and filter change interval recommendations closely match today's operating environments.

Local conditions, severity of operation or duty cycle may require more or less frequent fluid change intervals that differ from the information contained in the following charts. Allison Transmission recommends that customers use fluid analysis as the primary method for determining fluid change intervals for those vehicles not equipped with prognostic software. In the absence of a fluid analysis program, the fluid change intervals listed in the following charts should be used.

If you have questions regarding fluid or filter change intervals, or models not listed in this brochure, additional information can be found at www.allisontransmission.com; click Service, then Fluids or Fluid/Filter Change Intervals. Or, contact the Allison Technical Assistance Center at 1-800-252-5283.

FLUIDS _____

Allison Transmission recommends that customers use an Allison Approved TES 295® automatic transmission fluid to extend drain intervals and to enhance transmission performance and durability in all operating environments with on-highway products.

Schedule One TES-389™ fluids may be used in traditional on-highway products but do not provide the same drain intervals or filter change intervals as Allison Approved TES 295.

TES 468™ fluids can be used anywhere a TES 295 product is specified. H 40 EP™ and H 50 EP™ products require use of a TES 468 approved fluid.

A complete list of approved fluids can be found at www.allisontransmission.com; click Service, then Fluids. C4 fluids and DEXRON®-VI are no longer recommended in any commercial on-highway transmission.

FLUID LOSS WITH FILTER CHANGE ONLY ____

When performing initial Main Filter change or changing Main and Lube Filters at recommended intervals, approximate fluid loss for each filter is as follows:

- 1000 and 2000 Product Families Transmissions Control Main Filter = 1 pint (0.47 liters)
- 3000 and 4000 Product Families Transmissions
 Main Filter = 2 quarts (1.9 liters)
 Lube Filter = 8 quarts (7.6 liters)







P	RΠ	CN	ns1	בורפ

Model Year 2009 and 2010 Prognostics:

Prognostics that monitor and maximize fluid and filter life were offered in Model Year 2009 for 1000/2000/3000/4000 Product Families. 3000/4000 Product Families Transmissions began using Prognostics with serial numbers 6510822005, 6520099957, 6610257671, 6620007438. 1000/2000 Product Families Transmission Prognostics were first available in July of 2008 (MY2009). MY2009 Allison Prognostics must only be used with Allison Approved TES 295 fluids.

January 2010 Allison Prognostics are compatible with TES 295 and TES-389 approved fluids in 3000/4000 Product Families Transmissions starting with TCM calibration CIN 4C or later (4C-xxxxx-yyy-z) and all January 2010 1000/2000 Product Families Transmissions.

All 3000/4000 Product Families Transmissions utilizing Prognostics require the use of Allison High Capacity filters. All 1000/2000 Product Families Transmissions utilizing Prognostics require the use of Allison control main spin-on filter, P/N 29539579. 1000/2000/3000/4000 Product Families Transmissions may or may not have this feature "enabled" or turned ON. This option requires that the OEM provide the wiring necessary and the feature enabled in the TCM. Refer to the appropriate operator's manual for the methods of identifying if Prognostics is enabled.

High Capacity Filters allow extended filter change intervals when used with an Allison Approved TES 295 automatic transmission fluid.

High Capacity Filters can be identified by P/N 29545777 or P/N 29545780 stamped into the filter end cap. Prior filters (non-high capacity) for Allison 3000/4000 Product Families transmissions can be identified by P/N 29538231 or P/N 29538232 stamped into the filter end cap.

3000/4000 Product Families	High Capacity Filter Kit		
	2 Inch Filter Kit P/N 29548987		
	4 Inch Filter Kit P/N 29548988		

Extended fluid and filter change intervals are only allowed with an Allison Approved TES 295 automatic transmission fluid and Allison High Capacity Filters. Filters must be changed at or before recommended intervals.

For a list of current Allison Approved TES 295 automatic transmission fluids, go to www.allisontransmission.com; click on Service, then Fluids.

1000/2000 SERIES Fluid and Filter Change Interval Recommendations						
			PROGNOSTICS TURNED OFF OR NOT CALIBRATED IN TCM		PROGNOSTICS TURNED ON	
		DUTY CYCLE	ALLISON Approved Tes 295® Fluid	ALLISON Approved Tes-389™ Fluid	ALLISON Approved Tes 295® Fluid	ALLISON Approved Tes-389™ Fluid
FLUID		General*	150,000 Miles (240,000 km) or 4,000 Hours or 48 Months	50,000 Miles (80,000 km) or 2,000 Hours or 24 Months	When indicated by controller or	
		Severe**	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months	48 months, whichever occurs first	24 months, whichever occurs first (MY2010)
	Spin-On Control Main Filter	General*	50,000 Miles (80,000 km) or 2,000 Hours or 24 Months	50,000 Miles (80,000 km) or 2,000 Hours or 24 Months	When indicated by controller or 48 months, whichever occurs first	When indicated by controller or 24 months, whichever occurs first (MY2010)
		Control	50,000 Miles (80,000 km) or 2,000 Hours or 24 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months		
FILTERS	Internal Filter	All	Overhaul	Overhaul	Overhaul	Overhaul
	Lube/ Auxiliary Filter	Auxiliary	50,000 Miles (80,000 km) or 2,000 Hours or 24 Months	50,000 Miles (80,000 km) or 2,000 Hours or 24 Months	When indicated by controller or 48 months,	When indicated by controller or 24 months, whichever
			Severe**	(80,000 km) or 2,000 Hours or 24 Months	(20,000 km) or 500 Hours or 6 Months	whichever occurs first

NOTE: Change fluid and filters at or before the recommended mileage, months or hours have elapsed, whichever occurs first.

3000 SERIES **High Capacity Filters** Fluid and Filter Change Interval Recommendations

riuu anu riiter Change interval Recommendations								
			PROGNOSTICS TURNED OFF OR NOT CALIBRATED IN TCM		PROGNOSTICS TURNED ON			
		DUTY CYCLE	ALLISON Approved Tes 295® Fluid	ALLISON Approved Tes-389™ Fluid	ALLISON Approved Tes 295® Fluid	ALLISON Approved Tes-389™ Fluid		
FLUID		General*	300,000 Miles (480,000 km) or 6,000 Hours or 48 Months	25,000 Miles (40,000 km) or 1,000 Hours or 12 Months	When indicated by controller or	When indicated by controller or 24 months, whichever occurs first		
		Severe**	150,000 Miles (240,000 km) or 6,000 Hours or 48 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months	60 months, whichever occurs first			
	Main Filter	General*	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	25,000 Miles (40,000 km) or 1,000 Hours or 12 Months	When indicated by controller or 60 months, whichever occurs first	When indicated by controller or 24 months, whichever occurs first		
		Severe**	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months				
FILTERS	Internal Filter	All	Overhaul	Overhaul	Overhaul	Overhaul		
	Lube/ Auxiliary Filter	General*	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	25,000 Miles (40,000 km) or 1,000 Hours or 12 Months	When indicated by controller or	When indicated by controller or		
		Filter	Severe**	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months	60 months, whichever occurs first	24 months, whichever occurs first	

NOTE: Change fluid and filters at or before the recommended mileage, months or hours have elapsed, whichever occurs first.

^{*}General Vocation: All vocations not classified as Severe.
**Severe Vocation: 2000 MH, On/Off Highway, Refuse, City Transit, Shuttle Transit.

^{*}General Vocation: All vocations not classified as Severe.
**Severe Vocation: 2000 MH, On/Off Highway, Refuse, City Transit and and Shuttle Transit.

4000 SERIES High Capacity Filters Fluid and Filter Change Interval Recommendations

Fluid and Filter Change Interval Recommendations							
	PROGNOSTICS TURNED OFF OF NOT CALIBRATED IN TCM			PROGNOSTICS TURNED ON			
		TRANSMISSION MODEL	DUTY Cycle	ALLISON Approved Tes 295® Fluid	ALLISON Approved Tes-389™ Fluid	ALLISON Approved Tes 295® Fluid	ALLISON Approved Tes-389™ Fluid
FLUID		4000 w/	General*	300,000 Miles (480,000 km) or 6,000 Hours or 48 Months	25,000 Miles (40,000 km) or 1,000 Hours or 12 Months	When indicated by controller or	When indicated by controller or 24 months, whichever occurs first
		2" and 4" Sump	Severe**	150,000 Miles (240,000 km) or 6,000 Hours or 48 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months	60 months, whichever occurs first	
	Main Filter	4000 w/ 2" and 4" Sump	General*	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	25,000 Miles (40,000 km) or 1,000 Hours or 12 Months	When indicated by controller or 60 months, whichever occurs first	When indicated by controller or 24 months, whichever occurs first
	riilei		Severe**	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months		
FILTERS	Internal Filter	4000 w/ 2" and 4" Sump	All	Overhaul	Overhaul	Overhaul	Overhaul
	Lube/ Auxiliary Filter	4000 w/ 2" and 4" Sump	General*	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	25,000 Miles (40,000 km) or 1,000 Hours or 12 Months	When indicated by controller or	When indicated by controller or 24 months, whichever occurs first
			Severe**	75,000 Miles (120,000 km) or 3,000 Hours or 36 Months	12,000 Miles (20,000 km) or 500 Hours or 6 Months	60 months, whichever occurs first	

NOTE: Change fluid and filters at or before the recommended mileage, months or hours have elapsed, whichever occurs first.

FILTERS AND GASKET KITS WITH PARTS NUMBERS

1000/2000 Series						
Filter/Filter Kit Part Number						
Control Main	P/N 29539579					
Shallow Pan Suction (Overhaul Only)	P/N 29537965					
Deep Pan Suction (Overhaul Only)	P/N 29537966					
3000 Series						
2 Inch Filter Kit	P/N 29548987					
4 Inch Filter Kit	P/N 29548988					
4000 Series						
2 Inch Filter Kit	P/N 29548987					
4 Inch Filter Kit	P/N 29548988					

FLUID CAPACITY (APPROXIMATE)

1000/2000 Series							
Sump	Initial Fill		Refill				
	Liters	Quarts	Liters	Quarts			
Standard	14	14.8	10	10.6			
Shallow	12 12.7		7	7.4			
3000 Series							
Sump	Initial Fill		Refill				
	Liters	Quarts	Liters	Quarts			
4 Inch	27	29	18	19			
2 Inch	25 26		16	17			
4000 Series							
Sump	Initial Fill		Refill				
	Liters	Quarts	Liters	Quarts			
4 Inch*	45	48	37	39			
2 Inch*	38 40		30	31			

^{*}Add 2.8 liters (3 quarts) for transmissions with PTO.

NOTE: Approximate quantities do not include external lines and cooler hose. Fluid fill capacity is dependent on vehicle configuration. Final fluid capacity must be determined by dipstick level (see Mechanic's Tips MT3004EN Section 1 or your Operator's Manual under "Care and Maintenance").

^{*}General Vocation: All vocations not classified as Severe.
**Severe Vocation: 2000 MH, On/Off Highway, Refuse, City Transit and and Shuttle Transit.